

RODIM Smartmasking Plus Film

Published: 09.08.2017

Latest update: 15.09.2017

MASKING



Storage Remarks

Storage time is 12 months from delivery date. Keep storage temperature between + 20° C / ± 10° C and the relative humidity by 30 – 90%.

Storage in closed rooms. Avoid exposure of UV-radiation.

Available in:

Article number	Article description
45197808	RODIM Smartmasking Plus Film 6m x 100m
45197734	RODIM Smartmasking Plus Film 4m x 150m

Compatible with:

Article number	Article description
45130436	RODIM Dispenser for Masking Film

Packing:

1 Piece per box

Properties:

Property	Value & measuring unit	Measuring Method
Density	Ca. 1,0 g /cm ³	DIN EN 1183
Thickness	16 µm	GPA (Thickness Profile)

RODIM Smartmasking Plus Film

MASKING

Property	Value & measuring unit	Measuring Method
Tensile Strength machine direction	28,8 N / mm ²	ASTM D 882
Tensile Strength transverse direction	21,5 N / mm ²	ASTM D 882
Elongation at break machine direction	206 %	ASTM D 882
Elongation at break transverse direction	348 %	ASTM D 882
Dart drop	4,7 g / μm	ASTM 1709-91
Temperature stability	Until 125° C	

This technical information has been given to the best of our knowledge. The above-mentioned standards are average values and no granted assurance of special properties. This statement is limited to the material, in the state as it leaves the manufacturer and does not include possible modifications by conversion and/or handling after dispatch.